

MODEL No:	7303	
ISSUED:	1-87	
REVISED:	1-06	

## SPARE ROLL HOLDER





## **SPECIFICATION**

Spare Roll Holder shall be manufactured of stainless steel, alloy 18-8 type 304. Horizontal arm shall be 1/2" x 1" (13mm x 25mm) 21 gauge rectangular tubing with 18 gauge formed mounting flange and bracket welded on end. Roll holder post shall be 1" x 1" (25mm x 25mm) 20 gauge square tubing with closed ends and shall be welded to outer end. Mounting plate shall be provided and shall be 18 gauge. A stainless steel setscrew shall be provided on bottom of flange to lock unit to mounting plate. Surface finish shall be bright or satin as chosen by option and indicated by code suffix.

## **INSTALLATION**

Surface mount unit on wall using  $N^{\circ}$  10 self tapping screws (by others) through holes provided in mounting plate into suitable prepared mountings (by others) or other suitable mounting hardware (by others) to suit wall conditions. Hang post and flange assembly on mounting plate and tighten setscrew to lock unit to plate. For compliance with ICC/ANSI A-117.1-2003 and ADA Accessibility Guidelines, install unit so that top of horizontal paper holder arm is between 19" (483mm) minimum above finished floor (MIN AFF) to 40" (1016mm) maximum AFF (MAX AFF) and centerline of roll is no farther than 33" (838mm) from back wall behind commode or between 7" and 9" (178mm to 229mm) from front of commode. Recommended mounting height for general utility is 32" (813mm) AFF to top of post.

## **OPERATION**

One roll of toilet paper is placed over the horn type holder for use as required. Toilet paper is replenished on a cycle determined by maintenance needs.